

epT.I.P.S.® Packaging Options

eppendorf

Find the right purity grade for your applications!
Explore our Purity Selection Guide file [here](#)

Type of Tip	Bulk*	Box 2.0 filled with Tips**	Set (Box 2.0 + 5 Reloads)	Reloads	Racks (single use only)	Singles (single blister)
epT.I.P.S.® Eppendorf Quality 	0030000811 0030000838 0030000854 0030000889 0030000870 0030000900 0030000897 0030000927 0030000919 0030000935 0030000730 0030000951 0030000978 0030000650 0030000765 0030000781 	0030076125 0030076133 0030076141 0030076150 0030076168 0030076176 0030076184 0030076192 0030076206 0030076214 	0030076290 0030076303 0030076311 0030076320 0030076338 0030076346 0030076354 0030076362 	0030073371 0030073398 0030073410 0030073436 0030073452 0030073479 0030073495 0030073630 0030073517 	0030071638 0030071646 0030071654 	
epT.I.P.S.® BioBased Eppendorf Quality 	0030080033 0030080041 0030080050 0030080068 0030080076 0030080084 0030080092 0030080106 0030080114 0030080122 0030080130 					
epT.I.P.S.® PCR clean 				0030073754 0030073770 0030073797 0030073819 0030073835 0030073851 0030073878 0030073649 0030073894 	0030071662 	
epT.I.P.S.® Biopur® (sterile) 					0030075226 0030075234 0030075242 0030075250 0030075269 0030075277 0030075285 0030075293 0030075307 0030075315 	0030010027 0030010043 0030010060 
epT.I.P.S.® BioBased Biopur® (sterile) 				0030075420 0030075439 0030075447 0030075455 0030075463 0030075471 		
epT.I.P.S.® 384 Eppendorf Quality 			0030076273 0030076281 	0030076044 0030076052 		
epT.I.P.S.® 384 PCR clean 				0030076001 0030076010 		

Color of tip / volume

0.1 - 10 µL, dark gray

0.1 - 20 µL, medium gray

0.5 - 20 µL, light gray

0.5 - 20 µL, light gray, long tips

0.1 - 20 µL, light pink

5 - 100 µL, light yellow

2 - 200 µL, yellow

2 - 200 µL, yellow, yellow tips

20 - 300 µL, orange

20 - 300 µL, orange, yellow tips

50 - 1,000 µL, blue

50 - 1,000 µL, blue tips

50 - 1,250 µL, green

50 - 1,250 µL, dark green, long tips

0.25 - 2.5 mL, red

0.1 - 5.0 mL, violet

0.2 - 5.0 mL, violet, long tips

0.5 - 10 mL, turquoise

0.5 - 10 mL, turquoise, long tips

Distributed by Fisher Scientific. Contact us today:

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk
Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it
Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl
Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es
Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk



*Bulk: 1.000 tips for volumes 10 - 1,250 µL; 500 tips for volume 2.5 mL & 5 mL (120 mm); 300 tips for volume 5 mL (175 mm); 200 tips for volume 10 mL.
**Boxes/Trays of: 96 tips for volumes 10 - 1,250 µL; 48 tips for volume 2.5 mL; 24 tips for volume 5 - 10 mL.

Eppendorf®, the Eppendorf Brand Design and Eppendorf Tubes® epT.I.P.S.®, ep Dualfilter T.I.P.S.®, SealMax® are registered trademarks of Eppendorf SE, Germany.
All rights reserved, including graphics and images. Copyright © 2025 by Eppendorf SE.
Order No.: AA01 026 620/EN2/PDF/0225/MCP

ep Dualfilter T.I.P.S.® Packaging Options



Type of Tip	Reloads	Racks (single use only)	Singles (single blister)
ep Dualfilter T.I.P.S.® PCR clean/Sterile		10-1250µL: 10 Racks/96 Tips; 2,5mL: 5 Racks/48 Tips, 5mL (L): 5 Racks/24 Tips 0030078500 0030078519 0030078527 0030078535 0030078543 0030078551 0030078560 0030078578 0030078594 0030078586 0030078616 0030078624	0030077598
ep Dualfilter T.I.P.S.® BioBased PCR clean/Sterile	(10 Trays x 96 Tips) 0030081030 0030081048 0030081056 0030081064 0030081072 0030081080 0030081099 0030081102		
ep Dualfilter T.I.P.S.® SealMax® PCR clean/Sterile		(10 Racks x 96 Tips) 0030078691 0030078705 0030078713 0030078721 0030078730 0030078748	
ep Dualfilter T.I.P.S.® SealMax® BioBased Biopur® (sterile)	(10 Trays x 96 Tips) 0030081234 0030081242 0030081250 0030081269 0030081277		
ep Dualfilter T.I.P.S.® 384 PCR clean/Sterile		(10 Racks x 384 Tips) 0030078853 0030078861	
ep Dualfilter T.I.P.S.® Forensic DNA Grade		(10 Racks x 96 Tips) 0030078810 0030078829 0030078837 0030078845	

Find the right purity grade for your applications!
Explore our Purity Selection Guide file [here](#)

Color of tip / volume

0.1 - 10 µL, dark gray

0.1 - 10 µL, medium gray

0.5 - 20 µL, light gray

0.5 - 20 µL, light gray, long tips

0.1 - 20 µL, light pink

5 – 100 µL, light yellow

2 - 20 µL, yellow

2 - 100 µL, yellow

2 - 200 µL, yellow

20 - 300 µL, orange

50 - 1,000 µL, blue

50 - 1,250 µL, dark green, long tips

0.25 - 2.5 mL, red

0.1 - 5.0 mL, violet

0.2 - 5.0 mL, violet, long tips

0.5 - 10 mL, turquoise, long tips

Distributed by Fisher Scientific. Contact us today:

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk
Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it
Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl
Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es
Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk



Eppendorf®, the Eppendorf Brand Design and Eppendorf Tubes® epT.I.P.S.®, ep Dualfilter T.I.P.S.®, SealMax® are registered trademarks of Eppendorf SE, Germany.
All rights reserved, including graphics and images. Copyright © 2025 by Eppendorf SE.
Order No.: AA01 026 620/EN2/PDF/0225/MCP