



Black Light-Tight Conical Centrifuge Tubes

Ideal for additional protection of samples and reagents especially where shared storage facilities are being used.

- All tubes are specially constructed to prevent any leaching of black pigment
- 1.5mL have attached flat caps for easy one-handed use. Caps are pierceable if required
- 15mL and 50mL tubes have a detachable cap that will not tear the thread if accidentally over-tightened
- All caps are flat for easy labelling. The 1.5mL tube has a frosted labelling patch on the side of the tube, whilst the 15mL and 50mL tubes have a white lined space on the side
- Strong walls allow a high RCF rating for worry-free centrifugation
- Made from 100% virgin autoclavable polypropylene
- RNase, DNase and pyrogen-free with lot-to-lot traceability
- Compatible with all standard centrifuge rotors and storage racks and boxes designed for classic shaped conical tubes (i.e. 1.5mL tubes 18000xg; 15mL and 50mL 9400xg)

Ordering Information

Cat. No.	Description	Pack qty
1.5mL Conical Bottom Tube		
15386548	Black	500
15mL Conical Bottom Tube		
15396548	Black	500
50mL Conical Bottom Tube		
15306558	Black	500

Find out more at eu.fishersci.com

Austria: +43 (0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
 Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
 Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
 Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
 Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500