

Weighing boats

A full range of paper, polystyrene and aluminium weighing boats



Disposable paper weighing boats

A truly green solution to sample weighing

- A cost-effective solution to reduce plastics in the lab
- Made of greaseproof paper that meets FDA 21 CFR 176.170 (components of paper in contact with aqueous and fatty foods) and with 21 CFR 176.180 (contact with dry foods)
- Controls contents like a polystyrene weigh boat because they are easier to pour
- An alternative to regular weighing papers because they are easier to handle
- Available in a small and medium in both brown for light coloured samples and white for dark samples

Cat No.	Size	L x W x H	Colour	Pack qty
15422214	Small	35 x 35 x 15mm	Brown	500
15432214	Medium	45 x 45 x 15mm	Brown	500
15408113	Small	35 x 35 x 15mm	White	500
15442214	Medium	45 x 45 x 15mm	White	500

Polystyrene weighing boats

Flexible polystyrene boats feature smooth surfaces to provide accurate pour-outs with minimal sample loss

- Select white, black, or blue for best colour contrast to ensure sample is completely removed
- Biologically inert and resistant to dilute and weak acids, aqueous solutions, alcohols and bases Temperature range -10 to 70°C
- Can be used with microwave moisture analysers
- All are FDA/food-grade compliant
- Available in regular or anti-static material formulation
- Disposable

Standard square weighing boats

- Boats are shallow with a wide, flat bottom to resist tipping
- Rounded corners simplify transfer

Cat No. Regular material	Cat No. Antistatic material	Size	L x W x H	Colour	Pack qty
11593422	12922850	Small	46 x 46 x 8mm	White	500
11503432	11680302	Medium	85 x 85 x 24mm	White	500
11513432	12608513	Large	140 x 140 x 22mm	White	500
15728187	15768167	Small	46 x 46 x 8mm	Blue	500
15738187	15778167	Medium	85 x 85 x 24mm	Blue	500
15748187	15788167	Large	140 x 140 x 22mm	Blue	500
12982850	12942860	Small	46 x 46 x 8mm	Black	500
12992850	12952860	Medium	85 x 85 x 24mm	Black	500
12902860	12962860	Large	140 x 140 x 22mm	Black	500



Manufactured and packaged in a clean room

Hexagonal weighing boats

- Apply gentle pressure to these pointed flexible boats to form pouring spouts after weighing
- Flat bottoms and sloping sides provide accurate transfer

Cat No. Regular material	Cat No. Antistatic material	Size	L x W x H	Colour	Pack qty
-	15778187	Small	38 x 25 x 9mm	White	500
-	15788187	Medium	64 x 51 x 19mm	White	500
-	15798187	Large	102 x 76 x 22mm	White	500
-	15708197	X Large	127 x 89 x 31mm	White	500



Pour-boat weighing dishes

- Pour-spout design easily dispenses samples without flexing the dish
- Flat-bottom dishes are made from 12mm thick polystyrene for better strength, stability and handling

Regular material Cat. No	Antistatic material Cat. No	Size	L x W x H	Colour	Pack qty
15798177	15798167	Small	43 x 58 x 13mm	White	500
15708187	15708177	Medium	83 x 132 x 26mm	White	500
15718187	15718177	Large	108 x 183 x 26mm	White	500



Shallow weighing boats, square

- Shallow boat with a wide, flat bottom to resist tipping
- Ideal for solid product weighing

Regular material Cat. No	Antistatic material Cat. No	Size	L x W x H	Colour	Pack qty
15758187	-	Medium	90 x 90 x 7mm	White	500



Diamond weighing boats

- Diamond shape that easily flexes for accurate pouring
- Wide, flat bottom to resist tipping

Regular material Cat. No	Antistatic material Cat. No	Size	L x W x H	Colour	Pack qty
12932840	12992840	5mL	55 x 35 x 6mm	White	500
15768187	15718197	25mL	71 x 46 x 14mm	White	500
11573422	11533432	30mL	78 x 56 x 14mm	White	500
12387552	11543432	100mL	119 x 90 x 19mm	White	500
12952850	12912860	5mL	55 x 35 x 6mm	Black	500
15738197	15728197	25mL	71 x 46 x 14mm	Black	500
12962850	12922860	30mL	78 x 56 x 14mm	Black	500
12972850	12932860	100mL	119 x 90 x 19mm	Black	500



Aluminium weighing boats

For general-purpose weighing, dispensing, storage, food processing, evaporating, or drying

- Sturdy yet lightweight boats feature a smooth, flat bottom for sample handling and a flanged, crimped wall for rigidity
- Finger tab handle can be etched for identification prior to weighing

Regular material Cat. No	Size	Dimensions (D x H)	Pack qty
11998084	Small	43 x 12mm	100
11908094	Medium	57 x 14mm	100
11918094	Large	70 x 16mm	100
11988084	Large	101 x 8mm	50



© 2017 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at fisherbrand.com/trademarks.

Austria: +43 (0)800-20 89 40 Belgium: +32 (0)66 260 260 Denmark: +45 70 27 99 20
 Germany: +49 (0)2304 9325 Ireland: +353 (0)1 865 5854 Italy: +39 02 850 99 476
 Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 467 70 00
 Norway: +47 22 95 99 99 Portugal: +351 21 425 33 60 Spain: +34 902 238 303
 Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 600