

High-Volume Solvent Delivery Systems



Safety, efficiency and convenience

High-volume solvent delivery systems, available in 10L to 1000L, offer environmentally friendly solvent handling solutions for virtually unlimited applications, enhancing safety and improving productivity within your lab.

Enhanced solvent safety

High-volume solvent delivery systems incorporate safety features to protect the lab and the environment by offering a unique combination of mechanical and manual controls to prevent unwanted solvent flow. The bottle-free, closed system eliminates the potential for glass bottle breakage and makes the risk of spills and exposure to vapors negligible.

Reduce lab-operating costs

Increase lab efficiency by eliminating:

- Repeated solvent testing
- Multiple lots of material
- Bottle rinsing
- Disposal costs

Environmentally friendly solution

- Reduce the amount of solid waste generated in your laboratory
- Minimize the release of flammable or toxic solvent liquids and vapors
- Eliminate bottle rinsing – empty containers are returned, cleaned and refilled

For virtually unlimited applications

- High-performance liquid chromatography (HPLC)
- Preparative chromatography and high-volume gas chromatography sample preparation
- Process synthesis and extractions



Tailored solvents and solvent blends

Our catalogue range is developed for convenience, but our experience in developing, manufacturing, processing and testing high-purity solvents enable customization to your exact specification.

We can tailor make solvents to meet your specifications for your application. In addition, our dedicated solvent-mixing facilities are available to produce high-quality blends.

The quality of highly specified HPLC solvents can be compromised in handling and storage. Experience has shown that nothing other than a dedicated blending facility, designed for the purpose, can produce highly specified blends accurately and without introducing new impurities.

The facility

The new facility consists of '316 grade' stainless steel mixing vessels of 200L and 1,000L capacities situated in a dedicated zoned area. The vessels are fitted with air-driven stirrers and are situated on an electronic balance.

Solvents are charged by weight, through a 0.2-micron filter, by air-driven pump and/or by nitrogen pressure. Small amounts of solid and liquid additives are added via charge-ports. Hoses are made of PTFE and hose couplings are Hansen 'dry-break' type. All wetted surfaces are either PTFE or stainless steel.

Operating practices

All blending and mixing operations are carried out according to written procedures. The mixing vessels are cleaned (CIP) before and after the mixing/blending operation and are left in a dry condition, filled with nitrogen, between operations.



Product quality

On acceptance of a quotation for a 'bespoke' product, a sample will be prepared and the specification finalised with the customer. This specification will be formally defined in a document called a 'quality schedule' that will be signed by representatives of both Thermo Fisher Scientific and the customer. The quality schedule will be a full description of the customer's quality requirements, including packaging and labelling.

On manufacture, the components are charged and blended, and the resulting material is sampled to ensure the product quality. The material is then discharged into the final product containers by nitrogen pressure. The final product containers are then resampled and subjected to final testing and approval.

Packaging

The final product can be packaged in stainless steel containers of up to 1000L.

Ordering information

Products can be ordered through Fisher Scientific. However, we always recommend a technical review before purchase.

Please email your contact details and a brief description of your requirements to begel.sha.quotes@thermofisher.com

Quotations can also be requested from our website, www.wesupportyourchemistry.com

Before we provide product in returnable drums, documentation will need to be completed. This ensures that your delivery schedule can be met and gives complete contact details to facilitate the returns process.



For more information, contact your local distributor.

Austria

Fisher Scientific (Austria) GmbH
Rudolf von Alt-Platz 1
A-1030 Wien
Toll-Free Number: 0800 20 88 40
Fax: 0800 20 66 90
info.austria@thermofisher.com
www.at.fishersci.com

Belgium

Fisher Scientific
Clintonpark – Keppekouter
Ninovesteenweg 198
B-9320 Erembodegem
Tel: +32 (0) 56 260 260
Fax: +32 (0) 56 260 270
be.fisher@thermofisher.com
www.be.fishersci.com

Czech Republic

Fisher Scientific, spol. s r.o.
Kosmonautu 324
CZ-530 09 Pardubice
Tel: +420 466 798 230
Fax: +420 466 435 008
info.cz@thermofisher.com
www.thermofisher.cz

Denmark

Fisher Scientific
Industrivej 3
DK-3550 Slangerup
Tel: +45 70 27 99 20
Fax: +45 70 27 99 29
kundeservice@thermofisher.com
www.fishersci.dk

Finland

Fisher Scientific Oy
Ratastie 2
FI-01620 Vantaa
Tel: +358 802 76 280
Fax: +358 802 76 235
fisher.fi@thermofisher.com
www.fishersci.fi

France

Fisher Scientific FAS
Parc d'Innovation BP 50111
67403 Illkirch Cedex
Tel: +33 (0) 3 88 67 53 20
Fax: +33 (0) 3 88 67 11 68
fr.commande@thermofisher.com
www.fr.fishersci.com

Germany

Fisher Scientific GmbH
Im Heiligen Feld 17
D-58239 Schwerte
Toll-Free Number: 0800 3 47 43 70
Fax: 0800 3 47 43 71
info.germany@thermofisher.com
www.de.fishersci.com

Ireland

Fisher Scientific Ireland
Suite 3 Plaza 212
Blanchardstown Corporate
Park 2
Ballycoolin
Dublin 15
Tel: +353 01 885 5854
Fax: +353 01 899 1855
fsie.sales@thermofisher.com
www.ie.fishersci.com

Italy

Fisher Scientific
Tel: +39 02 953 28 258
Fax: +39 02 953 27 374
it.fisher@thermofisher.com
www.it.fishersci.com

The Netherlands

Fisher Scientific
Postbus 4
Scheepbouwersweg 1b
1120 AA Landsmeer
Tel: +31 (0) 20 487 70 70
Fax: +31 (0) 20 487 70 70
nl.info@thermofisher.com
www.fishersci.nl

Norway

Fisher Scientific
Frysjavaeien 33E
0884 Oslo
Tel: +47 22 95 59 59
Fax: +47 22 95 59 40
fisher.no@thermofisher.com
www.fishersci.no

Portugal

Fisher Scientific
Rua Pedro Alvares Cabral,
nº24, 3ºD
Edifício Euro - Infantado
2670-391 Loures
Tel: +351 21 425 33 50/4
Fax: +351 21 425 33 51
pt.fisher@thermofisher.com
www.pt.fishersci.com

Slovenia

Fisher Scientific d.o.o.
Parmova 53
SI-1000 Ljubljana
Tel: +386 597 31 494
Fax: +386 597 31 495
si.info@thermofisher.com
www.si.fishersci.com

Spain

Fisher Scientific
C/ Luis I, 9
28031 Madrid
Tel: +91 380 67 10
Fax: +91 380 85 02
es.fisher@thermofisher.com
www.es.fishersci.com

Sweden

Fisher Scientific
Box 9193
400 94 Göteborg
Tel: +46 31 352 32 00
Fax: +46 31 352 32 50
fisher.se@thermofisher.com
www.fishersci.se

Switzerland

Fisher Scientific AG
Wilstrasse 57
CH-5610 Wohlen
Tel: +41 (0) 56 618 41 11
Fax: +41 (0) 56 618 41 41
info.ch@thermofisher.com
www.ch.fishersci.com

United Kingdom

Fisher Scientific UK Ltd.
Bishop Meadow Road
Loughborough
Leicestershire LE11 5RG
Tel: +44 (0)1509 555500
Fax: +44 (0)1509 555111
fsuk.sales@thermofisher.com
www.fisher.co.uk