

Fisherbrand CO₂ Incubators

Value for everyday cell culture

Choose a CO₂ incubator you can trust.

Fisherbrand™ CO₂ incubators provide an ideal growth environment, simple touch screen technology, and easy cleaning with high temperature decontamination.

Features include:

- 150 L stackable, polished stainless steel interior chamber
- Established direct heat technology for a reliable, uniform culture environment
- Gentle, fan-assisted air circulation designed to ensure homogeneous conditions and fast recovery of all conditions
- On-demand 90°C moist heat high temperature decontamination cycle does not require the removal of components or sensors; effective against a wide-range of contaminants (bacterial, mold, fungal spores, mycoplasma)
- Interactive, instinctive at-a-glance monitoring with touchscreen controller
- Integrated humidity reservoir for rapid recovery after a door opening
- Avoid dry-outs with built-in water level sensor with on screen prompts
- Two year warranty, parts and labor



At glance performance monitoring featuring on-screen menu prompts, error logs, and multiple language selection



Fisherbrand CO₂ Incubators

Ordering Information

Fisherbrand CO ₂ Incubators	
Cat. No.	Description
15660667	Fisherbrand CO ₂ incubator, stainless steel 150 L, chamber with on-demand 90°C decontamination cycle and thermal conductivity (TC) CO ₂ sensor technology, 230 V 50/60 HZ
15650667	Fisherbrand CO ₂ incubator, stainless steel 150 L, chamber with on-demand 90°C decontamination cycle and infrared (IR) CO ₂ sensor technology, 230 V 50/60 HZ

Specifications

Fisherbrand CO ₂ Incubators	
Construction	
Chamber Type	Direct Heat
Chamber Capacity	150 L
Internal Dimensions (w x h x d)	47 x 60.7 x 53 cm
External Dimensions (w x h x d)	63.7 x 86.7 x 76.6 cm
Operating Weight	70 kg
Shelf Dimensions	42.3 x 44.5 cm
Number standard/Maximum	3/10
Access Port	Standard
Temperature	
Range	0.3°C above ambient to 55°C
Control	±0.1°C
Uniformity	±0.5°C
CO ₂	
Range	1-20%
Control	±0.1%
Type	TC or IR
Humidity	
Type/Source	3 L pan-less reservoir
Range	> 90% at 37°C
High Temperature Decontamination	
On-demand High Temperature Cycle	Standard
Cycle Temperature	90°C
Cycle Length	25 h
Electrical	
Display Type	Touchscreen
Voltage/Frequency	230 V 50/60 Hz
Alarm Contacts	Standard
Data output	RS232

Find out more at eu.fishersci.com

Austria: +43 (0)800-20 88 40 **Belgium:** +32 (0)56 260 260 **Denmark:** +45 70 27 99 20
Germany: +49 (0)2304 9325 **Ireland:** +353 (0)1 885 5854 **Italy:** +39 02 950 59 478
Finland: +358 (0)9 8027 6280 **France:** +33 (0)3 88 67 14 14 **Netherlands:** +31 (0)20 487 70 00
Norway: +47 22 95 59 59 **Portugal:** +351 21 425 33 50 **Spain:** +34 902 239 303
Sweden: +46 31 352 32 00 **Switzerland:** +41 (0)56 618 41 11 **UK:** +44 (0)1509 555 500